Steel Dryfix 8

The AISI 304/316 stainless steel helical bar, with a 8 mm diameter, is a high mechanical performance stainless steel helical bar for dry binding of structural elements using the Helifix patented installation system.

Thanks to its particular shape and manufacturing process, Steel Dryfix 8 acts like a huge self-tapping screw, gripping the support, after a pilot bore has been drilled. The bar is suitable to connect together elements in brick masonry, raw earth, tuff, timber and in certain cases even concrete elements according to the mechanical characteristics of the support.



- 1. Patented, system provided with CE mark
- 2. Excellent durability guaranteed by AISI 304/316 stainless steel
- 3. Quick and easy dry installation in any weather conditions, using the special Steel Dryfix 8 driver attachment
- 4. Adhesion can be certified on site by pull-out test
- 5. High tensile and shear strength
- 6. Limited invasiveness and aesthetic impact
- 7. Compatible with Steel Dryfix 8
 Connection Cap

kerakoll

kerakoll Code: E1037 2023/01 EN

Areas of application

- → Intended use:
 - Connecting wall panels, in cases in which the teeth are not attached together well
 - Break-fill work of damaged or cracked architraves
 - Break-fill work at the soffit of masonry arches
 - Break-fill work of decorative stone which decorates the structure at the back
 - Connection of wooden beam heads to the masonry support
 - Break-fill work of cracks in the masonry structure, made of brick, raw earth, tuff
 - Limitation of the crack

- Seismic improvement of walls with emerging inner debonding/collapse of parts of the masonry
- Binding for coating facades
- Anti-collapse connection for stud walls
- Construction of connections for Geosteel mesh band and mesh sheet strengthening elements, in combination with SteelDryfix 8 insert
- Creation of mechanical anchoring for protective systems for floors subject to breakaway of the bottom layer in combination with Steel Dryfix 8 Insert

Instructions for use

→ Preparation

The Steel Dryfix 8 bars must be cut before installation. Maximum installation length of 500 mm.

The installation will be done by means of the dedicated patented Helifix piling system.

→ Preparation of substrates

The masonry must be prepared following in the instructions dictated by the PM, if appropriate In the case of through cracks after installing the break-fill work bars, it is advantageous to proceed with filling the cracks with geo-mortar made of pure natural lime NHL and geo-binder (such as Geocalce G Antisismico or Geocalce F Antisismico) or Biocalce Pietra, depending on the support, and the injection of suitable slurry key to restore the material continuity of the masonry.

For historical walls, proceed with the injection of Geocalce FL Antisismico.

→ Application

Dry joining of masonry in brick or tuff using Steel Dryfix 8 should be followed by drilling a pilot bore with a appropriate diameter depending on the consistency of the substrate and with a length possibly equivalent to all the lengths of the break-fill work bar that must be installed.

After placing the Steel Dryfix 8 Driver attachment into the SDS Plus drill to engage, put the bar inside the pilot bore, tapping with percussion until it is completely inserted; after the bar has been inserted fill the end of the bore with the suitable geo-mortar (Geocalce G Antisismico, Geocalce F Antisismico, Geolite) or mineral epoxy adhesive (Geolite Gel), in a way that guarantees that the bore is perfectly sealed and that the hole opening is restored in a manner that guarantees perfect adhesion of the bar to the substrate also to the opening.

→ In order to assess the performance of adhesion/ extraction between different supports, you are advised to contact our technical office. Pull-out test is accomplished on site using a suitable test kit Steel Dryfix. kerakoll Code: E1037 2023/01 EN

Special notes

- → The bars are available in the length of 1000 mm. Steel Dryfix 8 bars can be cut to obtain different lengths (no longer than 500 mm).
- → The Steel Dryfix 8 Driver attachment is essential for installation, and is supplied in packs of one.

Certificates and marks



Abstract

The Steel Dryfix 8 AISI 304/316 stainless steel helical bar

Execution of reinforcement, and break-fill work of masonry made from brick, raw earth, tuff, wood and other material by means of Steel Dryfix 8 AISI 304/316 stainless steel helical bar, installed with Helifix technology in specified pilot bore in the structure, subject to possible repair of weakened surfaces, by means of the appropriate chuck supplied Steel Dryfix 8 Driver attachment which is tapped into position.

They include: (1) Making a pilot bore of a suitable diameter, according to the bar and to the material from which the element to be reinforced is composed; (2) Installing the bar inside the bore by means of the appropriate Steel Dryfix 8 Driver attachment and possible extension dependent on the bar length; (3) Possible filling of the bore with suitable material, which will depend on the type of support, that is: Geocalce G Antisismico, Geocalce F Antisismico or Biocalce Pietra, for masonry substrates; Geolite, for reinforced concrete supports; Geolite Gel for supports in reinforced concrete or other materials. The break-fill work bar must guarantee the minimum performance characteristics of the plan, in other words: tensile breaking load \geq 12.7 kN; shear breaking load \geq 7.2 kN; modulus of elasticity \geq 150 GPa; ultimate elongation at rupture \geq 4%; nominal area 11.00 mm².

The price is by unit of bar length actually laid.

delivery and installation of all the materials described above as well as everything else required to finish the job is included. The following are excluded: restoration of degraded areas and repair of the substrate; mortar to fill and mask the bore; material acceptance tests; pre- and post-procedure testing, all aids required to perform the work.

kerakoll Code: E1037 2023/01 EN

Technical Data compliant with Kerakoll Quality Standard			
Material			AISI 304/316 stainless steel
Nominal diameter	Ø	8 mm	
nominal area of the bar	$\mathbf{A}_{ ext{elica}}$	11 mm ²	
Tensile breaking load, typical value	N	≥ 12,7 kN	UNI EN ISO 6892-1:2016
Shear breaking load of the bar	T	≥ 7,2 kN	UNI EN 846-7
Elastic tensile strength ($\epsilon = 0.2\%$)	σ _{0,2%}	≥ 830 MPa	UNI EN ISO 6892-1:2016
Elastic modulus of the bar, average value	$\mathbf{E}_{ ext{barra}}$	≥ 150 GPa	UNI EN ISO 6892-1:2016
Break warp of the bar, characteristic value	٤ barra	≥ 4%	UNI EN ISO 6892-1:2016
Packs:			
- Bar length	1000 mm	Box. pc. 50	

Other lengths can be supplied on request and in the minimum order quantities stated. Delivery times will be agreed on each time

Warning

- → Product for professional use
- → abide by any standards and national regulations
- → when handling the material wear protective clothing and goggles, and follow the instructions regarding methods for applying the material
- \rightarrow contact with the skin: no special measures required
- → storage on the work site: store under cover in a dry place, well away from substances that might damage it or its ability to adhere to the chosen matrix
- → the product is an item according to the definitions of the EC Regulation No. 1907/2006 and therefore does not require a Safety Data Sheet
- → for any other issues, contact the Kerakoll Worldwide Global Service +39 0536 811 516 globalservice@kerakoll.com



Kerakoll Quality System ISO 45001 CERTIFIED The Rating classifications refer to the GreenBuilding Rating Manual 2013. This information was last updated in December 2022; please note that additions and/or amendments to this information may be made over time by KERAKOLL Spa; for the latest version, see www.kerakoll.com. KERAKOLL SpA shall therefore be liable for the validity, accuracy and updating of information provided only when taken directly from its institutional website. The technical data sheet given here is based on our technical and practical knowledge. As it is not possible for us to directly check the conditions in your building site and the execution of the work, this information represents general indications that do not bind Kerakoll in any way. Therefore, it is advisable to perform a preliminary test to verify the suitability of the product for your purposes.